SERVICE PARTS LIST

K61A

Milwaukee

SPECIFY CATALOG NO. AND SERIAL NO. WHEN ORDERING PARTS

1-3/4" SDS-Max Rotary Hammer STARTING SERIAL

5546-21

CATALOG NO.

REVISED BULLETIN

DATE Aug. 2019

WIRING INSTRUCTION SEE PAGES 4 & 5






FIG. PART NO. DESCRIPTION OF PART (1) 21	21 42-62-0013 Side Handle Assembly (1) 21a 31-05-0011 Clamping Ring (1) 21b 05-89-0015 Fixing Screw (1) 21c 45-88-0103 Flat Washer (1) 21d 43-72-0002 Holder 1 (1) 21e 43-72-0003 Holder 2 (1) 21f 05-55-0018 Hex Nut (2) 21g 44-66-0049 Support Plate (1) 21h 44-90-0046 Ring (1) 21h 44-90-0046 Ring (1) 21h 44-52-0013 Absorber Housing (2) 21k 44-52-0013 Absorber (1) 21m 43-87-0015 Bellows (1) 21m 43-24-0010 Extension (1) 21p 42-52-0031 Side Handle Cap (1) 21q 43-98-5316 Side Handle (1) 22 14-29-0013 Gearcase Assembly (1) 22e				•
47 16-01-0011 Armature Assembly (1) 48 02-04-0530 Ball Bearing (1) 49 18-01-0011 Field Assembly (1)		21 21a 21b 21c 21d 21e 21f 21h 21j 21k 21n 21p 22e 22f 42 43 44 45 46 47 48	42-62-0013 31-05-0011 05-89-0015 45-88-0103 43-72-0002 43-72-0003 05-55-0018 44-90-0046 43-76-0012 44-52-0013 43-87-0015 43-24-0010 42-52-0031 43-98-5316 14-29-0013 	Side Handle Assembly Clamping Ring Fixing Screw Flat Washer Holder 1 Holder 2 Hex Nut Support Plate Ring Absorber Housing Absorber Bellows Extension Side Handle Cap Side Handle Gearcase Assembly Flat Washer M6 x 10mm Pan Hd. Hex Drive Mach. Sc 8-32UNC x .313" Pan Hd. Taptite T-20 Sc O-Ring EM-Clutch Assembly M4 x 70mm Pan Hd. ST Phillips Screw Fan Baffle Armature Assembly Ball Bearing Field Assembly	(1) (1) (1) (1) (1) (1) (2) (1) (1) (1) (1) (1) (1) (1) (1) (1) (1
47 16-01-0011 Armature Assembly (1) 48 02-04-0530 Ball Bearing (1)	50 43-76-0013 Front Housing Support - Left (1)	47 48	16-01-0011 02-04-0530	Armature Assembly Ball Bearing	(1) (1)

FIG.	PART NO.	DESCRIPTION OF PART	NO. REC
54	05-88-0028	M6 x 55mm Pan Hd. Taptite T-30 Screw	(4)
55	22-18-0011 •	120V Carbon Brush Assembly	(1)
55a		120V Carbon Brush	(1)
55b		120V Carbon Brush with Cut-Off	(1)
56	22-22-0021	Brush Holder Assembly	(2)
57	05-78-5313	M4 x 9mm Pan Hd. Plastite T-15 Screw	(2) (2) (1)
58	42-92-0049	Bottom Cover	(1)
59		M4 x 18mm Pan Hd. ST T-20 Screw	(4)
60	14-20-0090	120V PCBA	(1)
61	23-66-0059	120V On-Off Switch	(1)
62		Switch Trigger	(1)
63	14-34-0012	Handle Service Kit	(1)
63a		Handle Support - Left	(1)
63b	42-42-0054 ●	Foam Bushing	(3) (1)
63c		Handle Cover - Right	
	44-66-0098	Auto Stop Plate	(1)
63e		LED Lens Holder Plate	(1)
63f	44-06-0007	Working Lens with Ink Print	(1)
	44-06-0008	Working Lens	(1)
	05-78-5311	M5 x 18mm Pan Hd. ST T-20 Screw	(7)
	40-50-0059	Spring	(1)
	44-60-0074	Lock Button	(1)
63n		Speed Dial	(1)
	22-56-0475	Terminal Block	(1)
	31-17-0155	Cord Clamp	(1)
	06-82-0995	M4 x 16mm Pan Hd. Plastite T-20 Screw	/ (2) (1)
	22-64-0019	120V Power Cord with Strain Relief	
	22-56-0150	Closed End Connector	(3)
	12-20-0161	Service Nameplate	(1)
75	42-55-0073	Blow Molded Carrying Case	(1)
	23-94-0048	Ground Wire Assembly (Not Shown)	(1)








• 14-46-2719 MAINTENANCE SERVICE KIT

	TI	HIS KIT CONTAINS:
$\overline{}$		
1	45-12-5316	Rubber Dust Shield
1	34-60-5316	Retaining Ring
2	34-40-5316	Spindle O-Ring
2	34-60-5319	O-Ring
2	45-06-5317	Turcon Seal
2	34-40-5308	O-Ring
2	42-42-0054	Foam Bushing
1	14-46-5316	Bearing Shield Assembly
1	34-60-0072	Back Press Ring
2	34-60-0078	O-Ring
1	43-44-0012	Rubber Gasket
1	34-40-5309	O-Ring
1	44-90-5319	Spring Ring
3	49-08-5355	'Q2' Grease (2.8oz/80g tube)
1	22-18-0011	120V Carbon Brush Assembly
		•

FASTENER TORQUE SPECIFICATIONS (IN./LBS.)						
		SEATING TORQUE				
FIG. NO.	WHERE USED	in/lbs	kgf/cm	Nm		
34	Selector Bracket Clamp Plate	11	13	1.3		
38	Gearcase Cover	63	73	7.2		
47	Motor Housing	56	65	6.4		
48d	Housing Halve Cover	25	29	2.9		
48c	Housing Halve Cover	11	13	1.3		
50b	Coin Cell Cover	2.6	3.05	0.3		
39h	Selector Knob	16	18	1.8		
39h	On-Off Switch	11	13	1.3		
	Switch Termination Screws	8	10	1.0		
	Ground Screw-Gearcase	44	50	5.0		







BLK & WHITE From Control Board. Both black and white wires are terminated together. Connect with black & white wires from EM clutch.

(5) WHITE, BLUE, BLACK From Control Board to Hall Sensor Board.

7 WHITE From Control Board, connect to white field wire #14 using closed end connector.

(10) RED From Control Board, connect to red field wire #16 using closed end connector.

(3) GRN/Y From Power Cord to connect to green/ yellow wire #17 using closed end connector.

(14) WHITE From Field, connect to white wire #7 from control board assembly using closed end connector.

(5) BLACK From Field, connect to left brush holder assembly.

(16) RED From Field, connect with red wire #11 using closed end connector.

(7) GRN/Y Ground wire assembly, connect to green/yellow wire #13 using closed end connector.

(8) BLACK From Field, connect to right brush holder assembly.

(9) RED From Right Brush, connect to red wire #4 from control board.

